

Ansell

AnsellGUARDIAN[®] Chemical Report

Ansell

Ansell



Disclaimer

In this report, you will find information related to the barrier performance of certain personal protective equipment (PPE) against the chemicals you selected. This information is intended to enable the Health and Safety professional at your organization make more informed decisions about the Ansell PPE that may offer the greatest protection in the intended circumstances and assist with carrying out a risk assessment for your organization.

We wish to highlight that permeation times do not equate to safe wear time. Safe wear time may vary depending on whether the PPE is donned correctly, the surrounding temperature, the chemicals' toxicity, and other factors. Permeation information offered here is limited to the main protective material. Permeation times may vary around seams, zips, visors or any other joins or components of the PPE. It is the responsibility of your organization's Health and Safety professional to undertake a risk assessment before choosing the appropriate PPE for the task at hand. If you want to discuss any aspect in detail, please contact us.

Estimations of the barrier properties of PPE are based on currently available data and extrapolations from laboratory test results and information regarding the chemicals' composition. Synergistic effects of mixing chemicals have not been accounted for. Estimations are subject to change if new testing is carried out or new information is available providing better grounds for extrapolations. For these reasons, any information in this report is provided for informational purposes only and Ansell fully disclaims any liability including warranties related to any statement contained herein.

Legend for Hand Protection

Permeation Breakthrough Times		
<10	Not Recommended	
10-30	Splash Protection	
30-60	Splash Protection	
60-120	Medium Protection	
120-240	Medium Protection	
240-480	Good Protection	
>480	Good Protection	

Permeation breakthrough time is the time (in minutes) for the chemical in question to be permeating through the material at a rate of $1.0 \mu\text{g} / \text{cm}^2 / \text{min}$ (as per EN ISO 374) or $0.1 \mu\text{g} / \text{cm}^2 / \text{min}$ (as per ASTM F739).

PS = Physical State: A = Aerosol, G = Gas, L = Liquid, P = Paste, S = Solid



Product Group : 23-200.201.202
 Brand : AlphaTec®
 Material : PVC
 Thickness (mm) : N.A.

The permeation breakthrough times present in this chart were evaluated according to the EN ISO 374 and ASTM F739 standard. Colored cells with numbers and symbol (C) correspond to experimentally determined data generated by an accredited laboratory.

CAS	Chemical Name	%	PS	EN ISO 374	ASTM F739
64-19-7	Acetic acid	100.0	L	171' c	120' c
1336-21-6	Ammonium hydroxide	35.0	L	82' c	64' c
62-53-3	Aniline	100.0	L	115' c	103' c
246538-78-3	C11-13 isoparaffin	100.0	L	360' c	215' c
56-23-5	Carbon tetrachloride	100.0	L	58' c	22' c
108-39-4	Cresol (m-)	100.0	L	> 480' c	> 480' c
108-94-1	Cyclohexanone	100.0	L	128' c	111' c
68476-34-6	Diesel fuel no 2	100.0	L	> 480' c	> 480' c
109-89-7	Diethylamine	100.0	L	16' c	22' c
141-43-5	Ethanolamine	100.0	L	> 480' c	> 480' c
107-21-1	Ethylene Glycol	100.0	L	> 480' c	> 480' c
50-00-0	Formaldehyde	37.0	L	> 480' c	
50-00-0	Formaldehyde	50.0	L	> 480' c	
86290-81-5	Gasoline	100.0	L	37' c	25' c
7647-01-0	Hydrochloric acid	37.0	L	> 480' c	> 480' c
7664-39-3	Hydrofluoric Acid	40.0	L	> 480' c	> 480' c
7722-84-1	Hydrogen peroxide	50.0	L	> 480' c	65' c
67-56-1	Methanol	100.0	L	57' c	32' c
71-23-8	n-Propanol	100.0	L	238' c	127' c
64742-49-0	Naphtha, petroleum, hydrotreated light	100.0	L	123' c	105' c



Product Group : 23-200.201.202
 Brand : AlphaTec®
 Material : PVC
 Thickness (mm) : N.A.

The permeation breakthrough times present in this chart were evaluated according to the EN ISO 374 and ASTM F739 standard. Colored cells with numbers and symbol (C) correspond to experimentally determined data generated by an accredited laboratory.

CAS	Chemical Name	%	PS	EN ISO 374	ASTM F739
7697-37-2	Nitric acid	70.0	L	149' c	205' c
7664-38-2	Phosphoric acid	85.0	L	> 480' c	> 480' c
63148-62-9	Silicone oil	100.0	L	> 480' c	> 480' c
1310-73-2	Sodium Hydroxide	40.0	L	> 480' c	
8052-41-3	Stoddard solvent	100.0	L	> 480' c	328' c
7664-93-9	Sulfuric acid	96.0	L	120' c	
108-88-3	Toluene	100.0	L	14' c	16' c