

Ansell

AnsellGUARDIAN<sup>®</sup> Chemical Report

Ansell

Ansell



## Disclaimer

---

In this report, you will find information related to the barrier performance of certain personal protective equipment (PPE) against the chemicals you selected. This information is intended to enable the Health and Safety professional at your organization make more informed decisions about the Ansell PPE that may offer the greatest protection in the intended circumstances and assist with carrying out a risk assessment for your organization.

We wish to highlight that permeation times do not equate to safe wear time. Safe wear time may vary depending on whether the PPE is donned correctly, the surrounding temperature, the chemicals' toxicity, and other factors. Permeation information offered here is limited to the main protective material. Permeation times may vary around seams, zips, visors or any other joins or components of the PPE. It is the responsibility of your organization's Health and Safety professional to undertake a risk assessment before choosing the appropriate PPE for the task at hand. If you want to discuss any aspect in detail, please contact us.

*Estimations of the barrier properties of PPE are based on currently available data and extrapolations from laboratory test results and information regarding the chemicals' composition. Synergistic effects of mixing chemicals have not been accounted for. Estimations are subject to change if new testing is carried out or new information is available providing better grounds for extrapolations. For these reasons, any information in this report is provided for informational purposes only and Ansell fully disclaims any liability including warranties related to any statement contained herein.*

## Legend for Hand Protection

---

Permeation Breakthrough Times		
<10	Not Recommended	
10-30	Splash Protection	
30-60	Splash Protection	
60-120	Medium Protection	
120-240	Medium Protection	
240-480	Good Protection	
>480	Good Protection	

Permeation breakthrough time is the time (in minutes) for the chemical in question to be permeating through the material at a rate of  $1.0 \mu\text{g} / \text{cm}^2 / \text{min}$  (as per EN ISO 374) or  $0.1 \mu\text{g} / \text{cm}^2 / \text{min}$  (as per ASTM F739).

PS = Physical State: A = Aerosol, G = Gas, L = Liquid, P = Paste, S = Solid



Product Group : 38-628  
 Brand : AlphaTec®  
 Material : Viton Butyl  
 Thickness (mm) : 0.7 mm / 27.6 mil

The permeation breakthrough times present in this chart were evaluated according to the EN ISO 374 and ASTM F739 standard. Colored cells with numbers and symbol (C) correspond to experimentally determined data generated by an accredited laboratory.

CAS	Chemical Name	%	PS	EN ISO 374	ASTM F739
95-49-8	2-Chlorotoluene	100.0	L	> 480' c	
122-99-6	2-Phenoxyethanol	100.0	L	> 480' c	> 480' c
107-85-7	3-Methylbutylamin	100.0	L	> 480' c	
64-19-7	Acetic acid	100.0	L	> 480' c	> 480' c
67-64-1	Acetone	100.0	L	> 480' c	
75-05-8	Acetonitrile	100.0	L	> 480' c	
7664-41-7	Ammonia, gas	100.0	G	> 480' c	> 480' c
62-53-3	Aniline	100.0	L	> 480' c	> 480' c
100-66-3	Anisole	100.0	L	43' c	34' c
71-43-2	Benzene	100.0	L	> 480' c	
75-15-0	Carbon disulfide	100.0	L	> 480' c	
7782-50-5	Chlorine, gas	100.0	G	> 480' c	> 480' c
123-42-2	Diacetone Alcohol	100.0	L	> 480' c	
111-92-2	Dibutylamine	100.0	L	> 480' c	> 480' c
75-09-2	Dichloromethane	100.0	L	83' c	
109-89-7	Diethylamine	100.0	L	57' c	
28454-70-8	Diisononylamin	100.0	L	122' c	
108-20-3	Diisopropylether	100.0	L	16' c	8' c
927-62-8	Dimethylbutylamine	100.0	L	> 480' c	> 480' c
68-12-2	Dimethylformamide	100.0	L	> 480' c	



Product Group : 38-628  
 Brand : AlphaTec®  
 Material : Viton Butyl  
 Thickness (mm) : 0.7 mm / 27.6 mil

The permeation breakthrough times present in this chart were evaluated according to the EN ISO 374 and ASTM F739 standard. Colored cells with numbers and symbol (C) correspond to experimentally determined data generated by an accredited laboratory.

CAS	Chemical Name	%	PS	EN ISO 374	ASTM F739
111-43-3	Dipropyl ether	100.0	L	9' c	9' c
141-78-6	Ethyl acetate	100.0	L	183' c	
110-71-4	Ethylene Glycol Dimethyl Ether	100.0	L	43' c	34' c
50-00-0	Formaldehyde	35.0	L	> 480' c	
142-82-5	Heptane	100.0	L	> 480' c	
392-56-3	Hexafluorobenzene	100.0	L	238' c	
7664-39-3	Hydrofluoric Acid	40.0	L	> 480' c	
7647-01-0	Hydrogen chloride	100.0	G	> 480' c	
7664-39-3	Hydrogen fluoride, gaseous	100.0	G	> 480' c	> 480' c
78-81-9	Isobutylamine	100.0	L	45' c	
27775-00-4	Isononylamin	100.0	L	122' c	
67-56-1	Methanol	100.0	L	> 480' c	
78-93-3	Methyl ethyl ketone	100.0	L	440' c	
127-19-5	N,N-Dimethylacetamide	100.0	L	> 480' c	
121-69-7	N,N-Dimethylbenzenamine	100.0	L	> 480' c	> 480' c
4637-24-5	N,N-Dimethylformamide dimethyl acetal	100.0	L	34' c	
123-86-4	n-Butyl acetate	100.0	L	132' c	
109-73-9	n-Butylamine	100.0	L	45' c	40' c
1126-78-9	N-Butylaniline	100.0	L	> 480' c	330' c
110-68-9	N-Butylmethylamine	100.0	L	42' c	32' c



Product Group : 38-628  
 Brand : AlphaTec®  
 Material : Viton Butyl  
 Thickness (mm) : 0.7 mm / 27.6 mil

The permeation breakthrough times present in this chart were evaluated according to the EN ISO 374 and ASTM F739 standard. Colored cells with numbers and symbol (C) correspond to experimentally determined data generated by an accredited laboratory.

CAS	Chemical Name	%	PS	EN ISO 374	ASTM F739
110-54-3	n-Hexane	100.0	L	> 480' c	
100-61-8	N-Methylaniline	100.0	L	> 480' c	> 480' c
7697-37-2	Nitric acid	70.0	L	> 480' c	
111-86-4	Octylamine	100.0	L	122' c	120' c
307-34-6	Perfluorooctane	100.0	L	> 480' c	
108-95-2	Phenol	90.0	L	> 480' c	
110-86-1	Pyridine	100.0	L	> 480' c	
1310-73-2	Sodium Hydroxide	40.0	L	> 480' c	
7664-93-9	Sulfuric acid	96.0	L	> 480' c	
1634-04-4	Tert-Butyl Methyl Ether	100.0	L	< 5' c	
127-18-4	Tetrachloroethylene	100.0	L	> 480' c	
109-99-9	Tetrahydrofuran	100.0	L	17' c	
108-88-3	Toluene	100.0	L	> 480' c	
102-82-9	Tributylamine	100.0	L	> 480' c	> 480' c
79-01-6	Trichloroethylene	100.0	L	> 480' c	
1330-20-7	Xylene, isomeric mixture	100.0	L	> 480' c	
	Hydrogen Fluoride (CAS# 7664-39-3, 17 C)		L	> 480' c	
	Hyjet IV-A Plus		L	> 480' c	306' c
	HYJET V		L	> 480' c	206' c



Product Group : 38-628  
Brand : AlphaTec®  
Material : Viton Butyl  
Thickness (mm) : 0.7 mm / 27.6 mil

The permeation breakthrough times present in this chart were evaluated according to the EN ISO 374 and ASTM F739 standard. Colored cells with numbers and symbol (C) correspond to experimentally determined data generated by an accredited laboratory.

CAS	Chemical Name	%	PS	EN ISO 374	ASTM F739
	Phenol (CAS#108-95-2, 45 C, molten)		L	> 480' c	> 480' c
	Phenol (CAS#108-95-2, 70 C, molten)		L	170' c	101' c
	Phenol 30%(CAS#108-95-2, at 70 C)		L	295' c	77' c
	Phenol 50%(CAS#108-95-2, at 70 C)		L	173' c	77' c